
Product Specification



DogBone Wet Inlay EPC Class 1 Gen 2, ISO 18 000-6C Impinj M730 Sales code 3007995

Mechanical dimensions

A1 x A2	Antenna size	94 x 24 mm	± 0,5 mm	3.701 x 0.945 in
B1 x B2	Die-cut size	97 x 27 mm	± 0,2 mm	3.819 x 1.063 in
С	Web width	100 mm	± 0,5 mm	3.937 in
D	Pitch, length per piece MD	30 mm	± 1,5 mm	1.181 in
E	Die-cut to web edge	1.5 mm	± 1,5 mm	0.059 in
F	Die-cut to register mark	0 mm	± 1,0 mm	0.000 in
I	Minimum size of register mark (width x length)	5 x 3 mm		0.197 x 0.118 in
U	Corner radius	3 mm		0,118 in



Electrical characteristics

Internated Circuit (IC)		Invaini M700
	Integrated Circuit (IC)	Impinj M730
	Air interface protocol	EPC Class 1 Gen 2, ISO 18000-63
	Operation frequency	860 - 960 MHz

Memory	128 bit EPC


General characteristics of transponder

Operating temperature (electronics parts)	-40 °C / +85 °C	-40 °F / 185 °F
ESD voltage immunity	± 2 kV peak HBM	
Shelf life: From the date of manufacture 2 years in	+20 °C, 50 % RH	68 °F, 50 % RH
Bending diameter (D)	> 50 mm, tension less than 10 N	

Delivery form

·			
Transponder format	Die-cut		
Transponder face material	Clear PET 12		
Transponder antenna material	Aluminum		
Transponder adhesive	RA-2		
- labelling temperature	min. +5 °C	min. 41 °F	
- usage temperature	-40°C - 150 °C	-40 °F - 302 °F	
- peel	min. 15 N / 25 mm (FTM 1)		
Final inspection	100 %, known faulty ones marked		
Minimum delivery yield	97 %		
	Reel number, Material number, Material description, Yield, Qty of functional inlays, Qty of non-functional inlays, Date		

Structure



Delivery details

Appearance	Single row reel form
Reel core	Paper core inner diameter 76 mm (3 in)
Winding of the reel	Face out
Reel size	5000 pcs/reel

Disclaimer:

SMARTRAC reserves the right to change its products and services at any time without notice. Our recommendations are based on our best knowledge and experience. As the products are used outside our control we cannot take responsibility for any damage that may be caused when using the product. Use extra care in handling the product.

This technical specification replaces all earlier ones.

Version

26 March 2021 Update date Author SMARTRAC /

Approved SMARTRAC / 3/29/2021 Kelvin Low/Smartrac







